



Push Paddle/Pull Paddle

Function

Pull Paddle

Push Paddle

Color/Finish



Dark Bronze


Satin
Aluminum

Handing Position / Opening Side

Left-Hand
Opening

Right-Hand
Opening

DESCRIPTION

Lever is reversible. Handing can be reversed on cam plug by removing C-clip and flipping the cam over and reinstalling C-clip. Cam plug is secured to lever by two hardened steel pins. Cam plug locks into deadlatch by use of set screw in deadlatch.

** Please note that a left-hand push paddle can be used as a right-hand pull paddle; or a right-hand push paddle can be used as a left-hand pull paddle by turning over and reversing the paddle from its original mounted position. However, it is preferable that you purchase the exact unit that you require. **

ADVANTAGES AND BENEFITS

Specifications: Lever: Cast aluminum alloy Escutcheon: 1 3/8" x 4" aluminum, heavy-duty spring mechanism prevents sagging of lever handle Spindle: Wrought steel, 1/4" square, hardened and heat-treated Hand: Non-handed, easily reversible Operation: Turning lever downward will activate deadlatch Standard package: Cam plug, all mounting screws, templates and installation instructions included Finish: AL - Satin Aluminum, BZ - Anodized Bronze Suitable for aluminum and steel doors Suitable for doors 1-3/4" thick

AVAILABLE PRODUCTS

Product #	Function	Color/Finish	Handing Position / Opening Side
CDH6792	Pull Paddle	Dark Bronze	Left-Hand Opening
CDH6794	Pull Paddle	Satin Aluminum	Left-Hand Opening
CDH6796	Pull Paddle	Satin Aluminum	Right-Hand Opening
CDH6793	Push Paddle	Dark Bronze	Right-Hand Opening
CDH6795	Push Paddle	Satin Aluminum	Left-Hand Opening
CDH6797	Push Paddle	Satin Aluminum	Right-Hand Opening

TECHNICAL SPECIFICATIONS

Door Thickness	1 3/4 in
Height	4.05 in
Backset	2 3/4 in
Usage	Hinge Door
Finish Warranty	5 Years
Mechanical Warranty	10 Years
Mounting Hardware	Included
Mounting Height	40 5/16 in
Dogging	1/4 in
Latchbolt Throw	3/4 in
Deadbolt Throw	1/2 in
Width	2.36 in
Length	5 in
Projection	2 1/2 in
Door Width Requirements	36 in
Projection Pushpad Neutral	2 1/2 in
Projection Pushpad Depressed	1 7/8 in

DISCLAIMER

Please note that a left-hand push paddle can be used as a right-hand pull paddle; or a right-hand push paddle can be used as a left-hand pull paddle by turning over and reversing the paddle from its original mounted position. However, it is preferable that you purchase the exact unit that you require.

PRODUCT PHOTOS

